## **Technology Offer**



TT-Ref. 2013-254





A simple, low cost, eco-friendly, fast, and easily up-scalable synthesis process for high permittivity silicone-based polymers and elastomers.

Background

Dielectric elastomer actuators (DEA) are stretchable capacitors that consist of a thin elastomeric film sandwiched between two compliant electrodes.<sup>[1]</sup> When a voltage is applied, an electrostatic force is acting on the film, which is compressed. Since elastomers con-serve their volume upon deformation, the film is elongated perpendicular to the applied electric field. This process is reversible; the polymer relaxes back to its original form after removal of the field. Common elastomers meet the mechanical requirements for actuators, however, they suffer from a low permittivity ( $\epsilon'$ ).<sup>[2]</sup> Therefore high driving voltages are needed to induce mechanical work which hinders applications in, for example, medical prosthetics or make the electronics complex and expensive.<sup>[3]</sup> A possible way to improve the performance is to increase  $\epsilon'$  of the elastomers. Herein, a low cost synthesis process for silicone elastomers with  $\epsilon'$  higher than 10 and excellent mechanical properties is presented which allowed the reduction of the driving voltage.

## **Advantages**

The preparation of these elastomers:

- is straightforward and allows tuning the dielectrical as well as the mechanical properties of the resulting materials,
- leads to homogenous materials in contrast to the commonly applied blending of higher permittivity phases into a silicone matrix,
- uses starting materials which are readily available and cheap, and
- is simple and up-scalable.



Our material shows 10% lateral strain at 8.5 V/µm

**Applications** The new materials can be used as dielectricum in dielectric elastomer actuators (DEA) technologies. Due to DEA simple working principle and their excellent properties that include lightweight, quiet muscle like actuation, high actuation strain and electromechanical efficiency, their application potential is imense, e.g. actuators, robotics, implantable prosthetic and rehabilitation devices, automotive and aeronautic industry, energy harvesting, sensors, and optical devices, to name a few.<sup>[3]</sup> Therefore, for all the above mentioned application, silicones with high permittivity are desirable.

Additionaly, materials with high permittivity are also interesting for capacitors and transistors.

- **Ownership** Empa, Swiss Federal Laboratories for Materials Testing and Research, Überlandstrasse 129, CH-8600 Dübendorf; *Patent pending*
- **References** [1] R. Pelrine, R. Kornbluh, Q. Pei, J. Joseph, Science, 2000, 287, 836–839.
  - [2] P. Brochu, Q. Pei, Macromol. Rapid Comm. 2010, 31, 10-36.
  - [3] F. Carpi, E. Smela, *Biomedical Applications of Electroactive Polymer Actuators,* Wiley–VCH, Weinheim, Germany, **2009**.
- **Keywords** High permittivity elastomers, high dielectric constant elastomers, dielectric elastomer actuators, silicone elastomers, silicone synthesis.

Contact	Empa, Technology Transfer Dr Andreas Kündig, andreas.kuendig@empa.ch Phone +41 58 765 48 30, Fax +41 58 765 69 08
Technical Information	Dr Dorina M. Opris, Laboratory for Functional Polymers dorina.opris@empa.ch Phone +41 58 765 43 04, Fax +41 58 765 11 22

Empa is an interdisciplinary research and service institution within the ETH Domain covering selected fields of materials science and technology development including important environmental issues. Empa's R&D activities focus on the requirements of industry and the needs of society, thus linking research to engineering, and science to industry and society. As a result, Empa is capable of providing its partners with customized services and solutions that not only enhance their innovative edge, but also help to improve the quality of life for the public at large. Safety, reliability and sustainability of materials and systems are cross-sectional topics and a hallmark of all Empa activities. As such, Empa plays a key role in Switzerland's research and innovation landscape.



Empa

**CH-8600 Dübendorf** Überlandstrasse 129

Telefon +41 58 765 11 11 Telefax +41 58 765 11 22

CH-9014 St. Gallen Lerchenfeldstrasse 5

Telefon +41 58 765 74 74 Telefax +41 58 765 74 99

**CH-3602 Thun** Feuerwerkerstrasse 39

Telefon +41 58 765 11 33 Telefax +41 58 765 69 90

www.empa.ch